



# Journey From Monochrome to Photorealism

Korean Design Guru  
Meets the Stratasys  
J Series 3D Printers



“

Our Stratasys 3D printer truly amazes everyone on the team, and boosts energy for designers to keep thinking out of the box for more and better ideas. We look forward to opening up a whole new world full of colorful and new designs together with Stratasys.”

Kim Young-se  
Innocode

# Journey From Monochrome to Photorealism

Korea-based Innodesign was founded in Silicon Valley in 1986 by design guru and unflinching innovator Kim Young-se. Chosen as one of the world's top 10 design groups by Nikkei BP in Japan 2009, Innodesign is known for adding winsome touches to the designs of many sought-after consumer products across the globe, such as LG Electronics' double-door refrigerator, Samsung's cutting-edge clamshell cellphone and Laneige's Foundation Sliding Pact.


As its name suggests, the company constantly looks for ways to improve and innovate their designs during the concept and rendering process. Kim often questioned why the design industry was not changing at the same pace as other industries going through digital transformations, until he was ushered into a new world by the Stratasys 3D Printer.

## 3D Print Photorealistic Prototypes With Ease

Even as an experienced user of digital fabrication technology including 3D printing, Kim was surprised by the unprecedented realism provided by the Stratasys J Series.

"Digital technology has become the backbone to support a person's wildest ideas and concepts, making things happen in the design world while keeping the concept as original as a model can be, regardless of its design complexity and fabrication technicality," Kim said.

With the Stratasys J Series, the Innodesign team brings new products to life by 3D printing models in multi-materials and in as many colors as their designers can assign. The multi-color, multi-material 3D printer adds value to the team in addition to the aesthetic benefits of prototypes. What used to be a monochromatic model has now become photorealistic prototype made possible





# Journey From Monochrome to Photorealism

through the automatic color mapping function, 360,000 color options and an unmatched range of materials.

To test the capability of the Stratasys 3D printer, Kim and his team used one of their headphone designs and mapped different patterns according to customer's original request. The result? "It was unexpectedly successful and everybody was happy about the fine details and the original color the 3D printer was able to reproduce," said Kim.

At the Stratasys launch event at the Dongdaemun Design Plaza, a hub famous for its cultivation in modern design coupled with cutting-edge technology, the audience was able to witness the multi-color, multi-material 3D printed headphones will full photorealism firsthand.

## Streamlined Post-Processing

Innocode says the Stratasys J Series 3D Printer is the first 3D printer that answers all of their needs in texture and color mapping, saving them massive amounts of time and cost in their conceptualization and professional rendering process. In their previous fabrication methods, 3D printed prototypes went through post processing steps, including sanding, lacquering and silicon engraving. With the Stratasys J Series, the team can take care of everything in fewer steps, giving them more time for their designs. Innocode has yet to find any drawback to the Stratasys 3D Printer.

3D printing enables Innocode to reproduce product-matching prototypes at a fraction of the original cost through traditional fabrication



# Journey From Monochrome to Photorealism

methods. Before 3D printing, creating a concept model cost the team \$900 to \$1,300 while producing a high-fidelity functional prototype cost \$2,700 to \$4,500. The Stratasys J Series 3D Printer, however, blurs the line between concept mockups and high-fidelity prototypes. Now, creating a functional prototype with full photorealistic patterns costs less than \$100. The time used in prototyping has also been reduced from two weeks to 8 hours, making the product development cycle more efficient and streamlining go-to-market plans for Innodesign and its partners.

“Our Stratasys 3D printer truly amazes everyone on the team, and boosts the energy for designers to keep thinking out of the box for more and better ideas. We look forward to opening up a whole new world full of colorful and new designs together with Stratasys,” concluded Kim.



	COST	LEAD TIME
Traditional Methods and post-processing	\$900-\$1,300	Up to 2 weeks
Stratasys J Series	\$88	8 hours
Savings	90%	97%

## Stratasys Headquarters

7665 Commerce Way,  
Eden Prairie, MN 55344  
+1 800 801 6491 (US Toll Free)  
+1 952 937-3000 (Intl)  
+1 952 937-0070 (Fax)

[stratasys.com](http://stratasys.com)

ISO 9001:2015 Certified

1 Holtzman St., Science Park,  
PO Box 2496  
Rehovot 76124, Israel  
+972 74 745 4000  
+972 74 745 5000 (Fax)

